



VentA Hood® WALL MOUNT LINER INSERT SPECIFICATIONS

BHPSLD LINER Equipped with halogen lighting. Not available with heat lamps.




BHPSLD

Connection Diagram (28 3/8" - 52 3/8" Widths)




600 CFM B200 Dual Blower (Top View)

Connection Diagram (46 3/8" - 58 3/8" Widths)




900 CFM B200 Dual & B100 Single Blower (Top View)




VP562 Transition (Optional) For B300 (B200 Dual Blower & B100 Single Blower)


Connection Diagram (52 3/8" - 64 3/8" Widths)



1200 CFM Double B200 Dual Blowers (Top View)




VP563 Transition (Optional) For B400 (Double B200 Dual Blowers)



VP562/VP563 transition centers outlet over top of hood

Recommended Mounting Height*



*Recommended mounting height is for optimum performance.

Electrical/Mechanical Specifications For Blower Units

Model	Volts	Amps*	Hz	RPM	CFM SP@0.0"	Equivalent CFM*	CFM SP@0.1"	CFM SP@0.2"	CFM SP@0.3"	Minimum Round Duct Size	Sones#
B200 Dual	115	2.9	60	1550	600	900	531	480	430	8" (50 in. ²)	6.5
B200 Dual & B100 Single	115	4.4	60	1550	900	1350	804	725	655	VP562: 10" (79 in. ²)	6.3
Two B200 Duals	115	5.8	60	1550	1200	1800	1062	960	860	VP563: 12" (113 in. ²)	6.6

* Add 0.5 amp for each halogen light. Hoods are available halogen lights (2 lights: 30" - 41", 3 lights: 42" - 53", 4 lights: 54" - 66").
 * Because the Magic Lung® blower uses centrifugal filtration rather than conventional baffle or mesh filters, the Magic Lung® blower can handle cooking equipment with higher cubic feet per minute (CFM) requirements and can deliver equivalent CFM much more efficiently than other than other filtration systems. When comparing the Magic Lung® with other blower units made by other manufacturers, use the "Equivalent CFM".
 # Ratings in accordance with the Standard Test Code by the Energy Systems Laboratory of the Texas Engineering Experiment Station.

